

MAVOSPEC BASE – Plant Lighting Measurement

All measured photometric variables, including lumens, lux and cd/m^2 , indicate the brightness impression of the human eye in daylight, i.e. the spectrum of light is evaluated by means of the spectral sensitivity curve $V(\lambda)$. And thus the fundamental problem of using luxmeters or luminance meters for the measurement of plant lighting is the fact that they underrate blue (400 - 500 nm) and red (600 - 700 nm) light within the visible spectrum. People perceive light within these ranges with reduced spectral sensitivity, but in particular where plants are concerned, blue and red light is used intensively for photosynthesis. The above-mentioned photometric measured variables are therefore not suitable for the evaluation of plant lighting.

The plant lighting spectrum can be measured and indicated by the MAVOSPEC BASE spectrometer from GOSSEN. It provides an initial indication as to whether or not and to what extent the wavelength ranges required for plant growth are available. The MAVOSPEC BASE now also determines photosynthetic photon flux density PPF (400 - 700 nm) over the entire spectral range and subdivided into the ranges PPF_{blue} (400 - 500 nm), PPF_{green} (500 - 600 nm) and PPF_{red} (600 - 700 nm), as well as the neighboring ranges PPF_{UV} (380 - 400 nm) and PPF_{FR} (700 - 780 nm). And thus the respective effect of plant lighting on growth, blossoming and the flavor of the respective plant can be evaluated to a great extent and adjusted. Measured values can be recorded during the course of the day with the help of a notebook and the Excel data logging template.

MAVOSPEC BASE owners can download the firmware update free of charge from GOSSEN's website at www.gossen-photo.de. Comprehensive information concerning the measurement of plant lighting is also available from GOSSEN's website under the BLOG heading.

Further information:

GOSSEN Foto- und Lichtmesstechnik GmbH, Lina-Ammon-Str. 22, D-90471 Nuremberg

Klaus-Peter Richter, phone: +49 911 800621 10, e-mail: klaus-peter.richter@gossen-photo.de

Horticulture Lighting Metrics




If you are dealing with lighting systems for greenhouses or plant growth, then you will find various information on the products offered by the manufacturers. These include watts, lumens, lux, cd / m^2 , PAR, PPF, PPFD and photon efficiency. We would like to give you a brief overview of which of these values are really relevant to the assessment of plant lighting and how they can be measured.

Perception of light

Humans and many other creatures perceive light differently than plants. The eye is differently sensitive to visible radiation depending on the wavelength. In daytime or photopic vision, the light sensitivity curve $V(\lambda)$ applies, which has its maximum at 555 nm (yellow-green). Color-sensitive uvulae in the eyes make it possible for us to recognize colors unequivocally. In the case of night or scotopic vision, the light sensitivity curve $V'(\lambda)$ applies, which has its maximum at 507 nm (blue-green). Light-sensitive rods in the eyes make it possible for us to see at these minimal levels of brightness, although we're no longer able to recognize colors.

All photometric measures, which include lumens, lux and cd / m^2 , reflect the brightness impression of humans in daytime vision. That means the spectrum of the light is evaluated with the light sensitivity curve $V(\lambda)$. The fundamental problem in using normal illuminance or luminance meters to measure plant illumination is the undervaluation of blue (400-500 nm) and red (600-700 nm) light in the visible spectrum. In these areas humans have only a reduced sensitivity, but especially plants use blue and red light intensively for photosynthesis. The above-mentioned photometric measurements are therefore not suitable for the assessment of plant lighting.



PAR

The photosynthetic active radiation PAR is the proportion of electromagnetic radiation from 400 nm to 700 nm of the visible light spectrum, which drive photosynthesis. The amount and the spectral composition of the PAR light are essential parameters for the assessment of horticulture lighting systems.

There are three aspects if you want to compare horticultural lighting systems:

- How much PAR, measured as photosynthetic photon flux PPF, does the system produce?
- How much PAR, measured as photosynthetic photon flux density PPFD, is arriving at the plants?
- How much energy is used by the system to generate the PAR for the plants? The measure for this is the photosynthetic photon efficacy PPE.

It makes limited sense to have only an integral value for PAR over the entire range of the spectrum because the effect on plants is spectrally dependent.

PPF

The photosynthetic photon flux PPF with the unit $\mu\text{mol/s}$ (micromoles per second) is the total PAR generated by a lighting system per second. This value is usually measured in the light laboratory with an integrating sphere and a special measuring device. It does not say how much of the measured light actually lands on the plant, but is an important measure of how to calculate the efficiency of a lighting system to produce PAR.

PPFD

The photosynthetic photon flux density PPFD with the unit of $\mu\text{mol}/\text{m}^2\text{s}$ (micromoles per square meter per second), is a measure of the amount of PAR that is actually available to plants. It represents the number of photosynthetically active photons falling on a given surface every second.

In the case of an illuminated planting area, it is not sufficient to measure at only one point, as there is usually no uniform illumination. Often the light intensity in the middle of the lighting system is strongest and decreases towards the edge of the crop surface. It is therefore advisable to define a measuring grid over the cultivated area, to carry out several measurements and to document the horizontal and vertical coordinates together with the measurement result. From the determined values, the mean value PPFD_{avg} and the irregularity $\text{PPFD}_{\text{min}} / \text{PPFD}_{\text{max}}$ can then be calculated.

Photosynthetic photon efficacy

The efficiency of a plant illumination system is often expressed as the ratio of the generated photosynthetic photon flux PPF in $\mu\text{mol}/\text{s}$ to the applied electrical power in watts (equal to Joules/s). The unit of efficiency is $\mu\text{mol}/\text{J}$ (micromoles per joule). The higher this number, the more electrical energy is converted into photosynthetic active radiation PAR, and the more efficient the lighting system is.

A frequent statement of the electrical power in watts, based on the illuminated area in m^2 is not meaningful, since it does not take into account the generated photosynthetic radiation PAR.

Measuring horticulture lighting

The MAVOSPEC BASE measures and displays the **spectrum** of the horticulture lighting system. It provides a first information whether the wavelength ranges required for plant growth are present and in which intensity they are present.

The MAVOSPEC BASE calculates the **photosynthetic photon flux density PPFD** over the entire spectral range and also divided into the areas blue, green, red. Following the PAR range, values for the UV and FR (Far Red) range are also provided. Thus, the respective effect of the horticulture lighting on growth, flowering and taste of each plant can be separately assessed and adapted. The following measuring values are available:

- **PPFD** 400 - 700 nm
- **PPFD_UV** 380 - 400 nm
- **PPFD_Blue** 400 - 500 nm
- **PPFD_Green** 500 - 600 nm
- **PPFD_Red** 600 - 700 nm
- **PPFD_FR** 700 - 780 nm

An **EXCEL template for data logging** makes it possible to record all measured values over the day with programable measuring interval.